

Model	Line	Standard
AUCKLAND	SKIPPER	EN ISO 20345:2011
Article	Protection	Availability in stock
94378-00L	S3 SRC	AVAILABLE

Preview



Sole



PU / PU ESD-plus SRC passed

PU double-density sole, light and comfortable. Designed mainly for indoor use with self-cleaning reliefs. New extra-grip PU tread with high SRC slip-resistant performance.

Removable Insole



Insole with modular support. Stronger on the calcaneus, ergonomic and softer on the waist edge, the comfort of memory foam and the functionality of Flyfit on the whole sole.

Protection Elements



New toecap "AluSxt 2.0" with differentiated functional thicknesses, and compensation rubber. Resistant to 200J. New "K+ Insole", resistant to the perforation of the carpenter nail of diameter 2,8 mm, in respect to the new tests for the future.

Type	Low Shoe
Upper	No ladder, High Tenacity textile, WR MicroFiber Suede with Pro-tech SXT light Airy, no ladder, WRU H.T. textile
Lining	Breezy 3D, two-layers combination
Antislip Lining	DUALMICRO
Removable	Soft-fit Plus ESD
Sole	PU / PU ESD-plus SRC passed
Toe Cap	Alu SXT 2,0
Anti-Perforation	K+ Anti-perforation PLUS
Size	40-48
Weight gr.	560

Working Environment

Logistics and Light Industry, Components and Automotive, ESD Areas.

SRC SRC (SRA+SRB)

Sole 94-95 PU - PU		
SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥ 0.32 HEEL CONTACT AREA ≥ 0.28	0.41 0.38
SRB STEEL + GLYCEROL	FLAT ≥ 0.18 HEEL CONTACT AREA ≥ 0.13	0.26 0.22

Antistatic



Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.

Features



Footwear suitable for "EPA" protected areas.
IEC EN 61340-5-1:2016
IEC EN 61340-4-3:2006

Symbols



Via A. Einstein, 6 - 35020 Casalsierugo (PD) - ITALY - Tel. +39 049 8740771 - Fax. +39 049 8741376 - mail info@maspica.it - www.sixton.it



Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.